

PERMANENT HAIR REMOVAL SYSTEM

PERFORMANCE AND SIMPLICITY ALL IN ONE



Choosing treatment parameters is quick and easy.

EIGHTEEN specific face and body areas that are preprogrammed according to different parameters:

mode, intensity and time







- IN THERMOLYSIS: When selecting the hair type to be treated, the Blend ST 250 will automatically choose the most efficient thermolysis technique to be used: Super Flash, Flash or Slow
- IN BLEND: When the area and hair type to be treated have been chosen, the Blend ST 250 automatically selects the appropriate and most efficient Blend technique for best results: Short, Pulsing or Uni Blend.
- IN MANUAL MODE: The Manual Mode offers direct access to the various modalities intensity and time parameters
 for customizing hair removal settings. Thermolysis, Blend as well as Electrolysis are all easily accessed through
 the digital keyboard.

With 250 programs and fully computerized controls, the Blend ST 250 easily competes with high performance upscale electrolysis systems.

BUILT-IN SILHOUET-TONE SPECIFICATIONS

Features:

- 4 Thermolysis modes
- 5 Blend modes (automatic UL calculation)
- 250 integrated programs to choose from
- 2 memory functions
- Choice of pedal or no pedal operation (insertion delay)

- Variable insertion delay mode
- Dual timer (Chrono or true time mode)
- Insertion counter (number of hair treated during session)
- Hydration test
- Accessories self-test

The many features and excellent quality/price ratio make the Blend ST 250 the standard permanent hair removal benchmark



Canada

2185 Michelin Street Laval, QC, Canada, H7L 5B8 1 866 340 9456 www.silhouettone.com

USA

2043 NW 87th Ave Miami, FL USA 33172 1 800 552 0418 www.silhouettone.us

Europe

Route de Suisse 9 1295 Mies (Genève) Suisse +41 22 775 15 60 www.silhouettone.com





